

STARTER KIT - DETERGENT AND DESCALER - 1 CAN 10LT ATCAL + 1 CAN 10LT DUAL ATCLEAN2

DUAL ATCLEAN²: liquid alkaline degreasing detergent for automatic washing and cleaning of Angelo Po professional ovens. Easily removes cooked and carbonized residues of fat, proteins and grease by emulsifying them and detaching them from the treated surfaces. ATCAL: liquid acid descaler for automatic washing and cleaning of Angelo Po professional ovens. It reduces the surface tension of the solution, makes it soluble and removes the accumulation of mineral hardness from the treated surfaces, facilitating rapid drying. The package includes: 1 10 It DUAL ATCLEAN² canister and 1 10 It ATCAL canister. For use on ovens: ACT.O (AT... models) - PRACTICO (TT... models).



Functional features

- · The kit includes the DUAL ATCLEAN² and ATCAL products.
- DUAL ATCLEAN² is a liquid alkaline degreasing detergent for automatic washing and cleaning of Angelo Po professional ovens. It easily removes cooked and carbonized residues of fat, proteins and grease by emulsifying them and detaching them from the treated surfaces. ATCAL is a liquid acid descaler for automatic washing and cleaning of Angelo Po professional ovens. It reduces the surface tension of the solution, makes it soluble and removes the accumulation of mineral hardness from the treated surfaces, facilitating rapid drying.
- HOW TO USE: use in undiluted form through the appropriate oven dosing system, selecting the available washing programs.
- COMPATIBILITY OF THE PREPARATION: the preparation is made and tested for maximum compatibility with the construction
 materials in Angelo Po ovens; do not use for purposes other than those intended. Do not replace the product with other
 detergents.
- PRECAUTION FOR HANDLING AND STORAGE: store in the original packaging away from extreme temperatures and direct light. The storage temperature can affect the fluidity of the formulation. Consult the safety data sheet.
- · USABLE: on ACT.O ovens (AT... models) PRACTICO (TT... models).
- The package includes: 1 10 It DUAL ATCLEAN² canister and 1 10 It ATCAL canister.
- The indications given have been established for general use conditions. In conditions that deviate from the norm, for example due to the particular hardness of the water, the working method or cleaning problems, we suggest consulting our technical service.
- The chemical-physical data indicated represent typical characteristics of the product deriving from the analyzes to which it is subjected. These values ??do not constitute specifications.

Technical Data

Dimensions

23x38x42 cm

