XS101S



BLAST CHILLER/FREEZER 45/27 KG/CYCLE

Blast chiller/freezer made of AISI 304 stainless steel. Production per cycle: 47 kg from +90°C to +3°C at product core in 90 minutes; 27 kg from +90°C to -18°C at product core in 240 minutes. Inner compartment useful for 10 levels, GN 1/1 or EN 60x40 containers. LCD control panel board and encoder, multipoint probe. It can be connected via Ethernet to the APO.LINK – Industry 4.0 – portal for real-time control of the appliances, and to export and view the data log and process parameters.



CE

Category	blast chiller - freezer	Cooling power	W 3136
Defrosting type	air	GN 1/1-EN tray insertion sid	32.5 - 40 cm
Max level/containers	nr. 10 GN 1/1 - 60X40	Production per cycle	45 kg (+90°C÷+3°C); 27 kg (+90°C÷-18°C)
Supplied core probe	IFR Multipoint		

Functional features

- Production per cycle: 45 kg from +90°C to +3°C at product core in 90 minutes; 27 kg from +90°C to -18°C at product core in 240 minutes.
- · Achievable temperature in chamber: -40°C.
- Control panel with monochromatic graphical display and encoder, allowing a multi-language management of each program with ease.
- I.F.R.: is a positive blast chilling system that automatically optimises the process for any type of food, no matter the size and quantity, chilling its surface thanks to the use of a multipoint, three sensor needle probe.
- SOFT +3°C: cycle carried out through probe at the core or time, suitable for chilling foods up to +3°C, using a chamber temperature of about 1°C.
- HARD +3°C: cycle carried out through probe at the core or time, suitable for chilling foods up to +3°C, using a chamber temperature varying from -15°C to -1°C.
- SOFT -18°C: cycle carried out through probe at the core or time, suitable for freezing foods up to -18°C, using a chamber temperature varying from 1°C to -36°C.
- HARD -18°C: cycle carried out through probe at the core or time, suitable for freezing foods up to -18°C, using a chamber temperature that can reach -36°C.
- INFINITY: time chilling/freezing cycle with infinite duration, suitable for cooling various type food pans. The temperature at the core can be checked.
- AUTOMATIC: manufacturer recommended work cycles. Possibility to select the type of food load. Nr 56 automatic cycles including: ANISAKIS 24h it is a special blast freezing cycle that enables preventive and total food preservation and restoration. Once the probe reads -20°C at the food core, the appliance will automatically start the "devitalization phase for 24 hours"; ANISAKIS 15h it is a special blast freezing cycle that enables preventive and total food preservation and restoration. Once the probe reads -35°C at the food core, the appliance will automatically start the "devitalization phase for 15 hours".
- STORED/ FAVOURITES: 10 chilling cycles and 10 freezing cycles that can be configured based on the needs of the user. 10 of these programmes can be made FAVOURITES.
- MULTY: time chilling/freezing cycle, organised by load levels, with possibility of needle probe reading, providing the time for each level.
- SMART ON: cycle with automatic start. Once a hot product is inserted if an increase in the chamber temperature is detected, after 5 minutes a Soft +3°C cycle will start, either by probe or time, based on whether or not the needle is used.
- STORAGE:. automatic activation of storage phase at end of blast chilling/blast freezing cycle Storing cycles and quick cooling cycles can be started separately.
- COOLING: it is ideal for pre-cooling the internal cell before the food loading, at an chamber temperature at around -25°C.
- MULTIPOINT PROBE: constant control of internal temperature and monitoring of operating anomalies, with signalling and saving
 of any variation.
- HACCP ALARMS: The presence of an alarm is indicated by the view on the display. The alarms are recorded on a list (nr. 30).



Angelo Po Grandi Cucine S.p.A. con socio unico - 41012 Carpi (MO) Italy - Strada Statale Romana Sud, 90 web: www.angelopo.com - email: angelopo@angelopo.it 29/11/2023

XS101S



 It can be connected via Ethernet to the APO.LINK – Industry 4.0 – portal for real-time control of the appliances, and to export and view the data log and process parameters.

Constructional features

- · Climate Class 4 (romm temperature 30°C, relative humidity 55%). Performances are guardanteed up to room temperature +32°C.
- · Forced ventilation not directly on foods. Air defrosting. Refrigerant gas: R452A. Air defrosting.
- One-piece construction with rounded internal corners. Exterior: AISI 304 stainless steel front, sides and top panels. Interior: AISI 304 stainless steel. Satin scotchbrite finish on door, side panels, control panel and top.
- · CFC-free expanded polyurethane insulation, 75 mm thickness, density 40kg/m³.
- · Hinged fan cover panel for easy access to the evaporator and fan during cleaning.
- · Copper/aluminium rustproofed evaporator.
- · Diamond inner floor for improved hygiene. Drain outlet for easy cleaning of interior.
- Inner compartment useful for 10 levels, GN 1/1 or EN 60x40 containers. 10 positions stainless steel demountable rack in wire AISI 304 stainless steel, clearance 71.5 mm.
- Door with self-closing system; outside full height stainless steel handle; easily-removable magnetic gasket; door frame heating element; magnetic door safety interlock for stopping inner fan motor; reversible on site.
- Stainless steel feet, height-adjustable from 105 to 155 mm.

Standard equipment

- Standard equipment: container rack. Plastic tray on the exterior bottom in order to facilitate defrosting water deposit.
- MULTIPOINT PROBE

Optionals and Accessories

Optional accessories: rack and runners kit rendering the chamber suitable for solely use of EN containers, UV lamp, probe fastener for liquid.

Technical Data			
Working voltage	400V 3N ~ 50 ÷60 Hz	Net Weight	175 kg
Gross Weight	200 kg	Electric Power	4 kW
Dimensions	80x83x185 cm	Packing	91x88x202 cm

